


## Razorbak™ Instructions




440C Grade high-carbon stainless steel blades set in a super-tough composite core for unbeatable strength


Super-sharp .039" thick main blade

Devastating .020" thick bleeder blades

The world's only cut-on-contact broadhead with rotating technology!  
Patent Pending.



**Exclusive Rotating Head Technology** allows the Razorbak to move to the path of least resistance for maximum penetration!



**Safety First!** To attach Broadhead:

Insert broadhead into arrow shaft. Insert wire wrench into ferrule hole and hold firmly. Turn **ARROW** to tighten broadhead onto shaft.  
Note: blade cartridge is designed to turn.

**HANDLE WITH EXTREME CAUTION - This product may be extremely dangerous and will cause injury if handled improperly.**  
**To avoid injury use the enclosed safety wrench when attaching and removing broadhead.**  
**Store heads in quiver after assembly.**